



MINI OSCILLATING TABLE

TE-143

Used for mixing liquids that are easily immiscible and that do not require a lot of stirring time for their homogenization.

Technical Characteristics

TE-143

- Rotation: 30 to 120 OPM;
- Rotation control: Analog;
- Motor: Direct current 100W;
- Cabinet: In carbon steel with anti-corrosion treatment and electrostatic painting;
- Dimensions: W = 385 x D = 345 x H = 195 mm (without platform);
- Weight: 16 kg;
- Power: 150 Watts;
- Voltage: 220 Volts;
- Accompanies: - 02 extra fuses - Instruction Manual with Warranty Term;

Benefits and Advantages

- Light aluminum tray with rubber to adhere the bottles
- Versatility: several types can be used (optional)
- Compact and easy to handle
- IEC plug international standard
- High grip feet in the shape of a suction cup for greater stability
- Handles for easy transport
- Easy-to-program analog rotation control (OPM)
- Strict Quality Control in which checks and tests guarantee the perfect functioning of the equipment providing safety and customer satisfaction
- Customer service to answer questions and provide explanations about the equipment and methodologies
- Possibility of adaptations according to the customer's needs makes the equipment already in line a special equipment.