



PENDULAR SHAKING TABLE

TE-240/1

Used for pendular agitation of separating funnels and other similar containers containing samples that need to be stirred for long periods for complete homogenization.

Technical Characteristics

TE-240/1

- Rotation: 30 to 300 BPM;
- Rotation control: Analog with digital display;
- Motor: 1/6 HP Induction;
- Timer: Digital - Programmable HH:MM. Automatic shutdown at the end of the programmed time;
- Platform: Rubberized with two adjustable separators;
- Cabinet: In carbon steel with anti-corrosive treatment and electrostatic painting;
- Dimensions: W = 700 x D = 540 x H = 370 mm;
- Weight: 37 kg;
- Power: 150 Watts;
- Voltage: 220 Volts;
- Accompanies: - 02 extra fuses - 02 Fixing screws;

Benefits and Advantages

- Rotation control (BPM) via easy-to-view digital display
- Easy-to-program digital timer
- Standard tray: built in such a way that you can use several bottle volumes because it has horizontally adjustable and rationable flaps
- Handle for easy transport
- IEC plug, international standard
- Robust rubber feet with high grip cushioning for greater stability
- Lower clamping system for installing the machine on a solid base for high speeds ensuring safety
- It can be used for long periods of work
- Strict Quality Control, in which checks and tests guarantee the perfect functioning of the equipment, providing safety and customer satisfaction
- Customer service, to answer questions and provide explanations about the equipment and methodologies
- Possibility of adaptations according to the customer's needs makes the equipment already in line a special equipment.