



DRYING AND STERILIZATION GREENHOUSE W CIRCULATION

TE-394/3-MP

Used for drying material glassware and samples in general and can be used to determine moisture whether or not it has a circulation and air renewal system.

Technical Characteristics

TE-394/3-MP

- Temperature: Ambient + 7 ° C to 150 ° C;
- Temperature control: Microprocessed digital with PID system and RBC calibration certificate;
- Sensor: Type 'J';
- Control accuracy: ± 1 ° C;
- Uniformity: ± 4 ° C;
- Capacity: 7 trays 115 mm apart;
- Motor: ¼ CV induction;
- Circulation system: Internal ventilation in the horizontal direction;
- Circulation / Renewal: Manual system to select the circulation type;
- Insulation: Thermal with double layer of ceramic fiber and glass wool;
- Safety: Overheat protection system;
- Sealing: Molded silicone door;
- Inner chamber: Polished stainless steel;
- Cabinet: In carbon steel with anti-corrosion treatment and electrostatic painting;
- Volume: 528 liters;
- External dimensions: W = 1310 x D = 750 x H = 1630 mm;
- Weight supported per tray: Up to 10kg;
- Weight: 200 kg;
- Power: 4000 Watts;
- Voltage: 220 Volts;
- Accompanies: - 03 Trays - Instruction Manual with Warranty Term;

Benefits and Advantages

- Double wall insulation allows better temperature control since it minimizes losses during the heating process
- This perfect insulation also allows for energy savings since the use of high power resistors is not necessary
- The stainless steel walls facilitate cleaning and are much more durable due to resistance against corrosion
- The safety thermostat works independently of microprocessor control and is activated in the event of a system failure preventing the temperature from exceeding the set limit
- Greater security and precision of the analysis
- Air circulation and renewal system providing an effective internal ventilation system promoting greater temperature homogeneity at different points within the greenhouses
- Air circulation and renewal system provides a more efficient and quick drying of the samples inserted there
- Air circulation and renewal system extends the service life of the stainless steel internal cabinet preventing corrosion.